

85U07538 ML160BC 50 Hz

Sound Measurement Report		
Sound Power measurement according to DS/ISO-3743		
Motor type: ML160BC	Product number: 85U07538	Fan diameter: D210 [mm]
P2: 18.5 [kW]	Pole: 2	

Remarks: The declared noise emission value, does not take production variations and measurement uncertainties into account. The declared value may therefore be up-to 3 dB higher, than the value for the average production unit.

Tested at:

Octave Band Level [db]									
Center Frequency	125	250	500	1000	2000	4000	8000	dB(A)	dB(lin)
Sound Power Level re: 1 pW									
Sound Pressure Average at 1m. re: 20 UPa									

