

87410026 MG160LB 60 Hz

DS/ISO-3743		
MG160LB	87410026	D210 [mm]
P2: 18.5 [kW]	2	
3dB		

[db]									
	125	250	500	1000	2000	4000	8000	dB(A)	dB(lin)
re:1 pW	66,9	68,4	73,6	73,2	70,5	69,0	65,7	77,8	78,9
1m, re:20 Upa	54,4	55,9	61,1	60,7	58,0	56,5	53,2	65,3	66,4

