

86187524 MG160MB 60 Hz

DS/ISO-3743		
MG160MB	86187524	D215 [mm]
P2: 11 [kW]	4	
3dB		

[db]									
	125	250	500	1000	2000	4000	8000	dB(A)	dB(lin)
re:1 pW	54,6	56,8	61,2	66,9	64,6	60,1	57,6	70,5	71,3
1m, re:20 Upa	42,1	44,3	48,7	54,4	52,1	47,6	45,1	58,0	58,8

