

86187524 MG160MB 60 Hz

Sound Measurement Report		
Sound Power measurement according to DS/ISO-3743		
Motor type: MG160MB	Product number: 86187524	Fan diameter: D215 [mm]
P2: 11 [kW]	Pole: 4	

Remarks: The declared noise emission value, does not take production variations and measurement uncertainties into account. The declared value may therefore be up-to 3 dB higher, than the value for the average production unit.

Tested at:

Octave Band Level [db]

Center Frequency	125	250	500	1000	2000	4000	8000	dB(A)	dB(lin)
Sound Power Level re: 1 pW	54,6	56,8	61,2	66,9	64,6	60,1	57,6	70,5	71,3
Sound Pressure Average at 1m. re: 20 UPa	42,1	44,3	48,7	54,4	52,1	47,6	45,1	58,0	58,8

Sound Pressure calculated according to ISO/DIS 11203 method Q2

