GRUNDFOS **INSTRUCTIONS**

Sololift2 C-3

115V/60Hz



be think innovate

GRUNDFOS


5.02 in. (127.3 mm)
1.60 in.
(40.6 mm)
4.75 in.
(120.7 mm)
6.24 in. (158.3 mm)
1.34 in. (34 mm)
14.00 in. (355.6 mm)
13.32 in. (338.2 mm)
7.92 in. (201 mm)
12.50 in. (317.5 mm)
13.43 in. (341.1 mm)
15.25 in. (387.4 mm)
17.82 in. (452.5 mm)
0.16 in. (4 mm)
1.50 in. (38 mm)


1x A
1x D
1x J
1x K
2x F
1x O
2x B
1x C
1x E
4x G
2x H
2x I
1x S
1x
1x T
2x P
2x Q
2x R




0.75“ / 1“ / 1.25“
(20mm/ 25 mm / 32 mm)
>1%
1.25“ / 1.5“
(32 mm /38mm)
0.75“ / 1“ / 1.25“
(20mm/ 25 mm / 32 mm)
1.5“ / 2“
(38mm / 51 mm)
Max. 20 ft. (6 m)
Min. 3.35 inch
(85 mm)
>2%
>2%


1.5“ / 2“
(38 mm/ 51 mm)
>1%
Max. 20 ft. (6 m)
1.5“ / 2“
(38 mm/ 51 mm)
1.5“ / 2“ (38mm / 51 mm)
>2%
>2%

v = 0.7 m/s
Ø


Max. 5 m
Max. 16 ft
3.7 m
12 ft
2.7 m
9 ft
1.8 m
6 ft
0.9 m
3 ft
1.25"
1"
0.75”
1.25"
(350 ft)
1.25"
(450 ft)
1.25"
(550 ft)
32 ft
65 ft
98 ft
131 ft
164 ft
196 ft
229 ft
295 ft
10 m
20 m
30 m
40 m
50 m
60 m
70 m
90 m
0.75”" inner-Ø 0.804 inch
1" inner-Ø 1.029 inch
1.25" inner-Ø 1.36 inch


4 x
+ 1 x



X

5 m	16 ft			1220	1378		118						1.5″
		2126	2126	98	157								1″
4 m	13 ft	1181	1181										0.75″
				2087	2283	315	551		20				1.5″
		3071	3071	354	433								1″
3 m	10 ft	1772	1772	98	177								0.75″
				2992	3150	748	945		276				1.5″
		4016	4016	630	709	59	118						1″
2 m	6.5 ft	2402	2402	276	374								0.75″
				3858	4016	1142	1378		512		118		1.5″
		4951	5039	906	984	197	256		39				1″
1 m	3.3 ft	3031	2992	472	551	39	98						0.75″
				4724	4882	1496	1811		787		276		1.5″
		5906	5906	1181	1260	354	394		138		20		1″
		3622	3622	669	748	138	197		59				0.75″
		8 gpm		16 gpm		24 gpm		32 gpm		40 gpm		48 l/s	
















I
T
I
S
R
Q
P


1


2


3
20°


4
0.4 inch
F
G
1.5“ / 2“
B


1.5“


2“


1.25“
1.5“
F
G
F


1
O
D
J


2
360°
A


3
F


1
D
J
O

2
A
360°


3
F
B
A


F
0.75”
K


F
1”


F
1.25”


1
Start 1 = 65 mm
Start 2 = 115 mm
Stop = 35 mm
3
2
Start 1
4
(Start 2)
Start 1


E
H






1


2A




Venting

GRUNDFOS Kansas City
17100 West 118th Terrace
Olathe, Kansas 66061
Phone: (913) 227-3400
Fax: (913) 227-3500

www.grundfos.us

GRUNDFOS Canada
2941 Brighton Road
Oakville, Ontario L6H 6C9
Canada
Phone: +1-905 829 9533
Telefax: +1-905 829 9512

www.grundfos.ca

GRUNDFOS Mexico
Boulevard TLC No. 15
Parque Industrial Stiva
Aeropuerto
C.P. 66600 Apodaca, N.L. Mexico
Phone: 011-52-81-8144 4000
Fax: 011-52-81-8144 4010

www.grundfos.mx

98822191 0515

ECM: 1159487

The name Grundfos, the Grundfos logo, and the payoff Be–Think–Innovate are registrated trademarks owned by Grundfos Management A/S or Grundfos A/S, Denmark. All rights reserved worldwide.

be think innovate

GRUNDFOS