

ALPHA SELECTION GUIDE



UPS3
THE SOLID
CHOICE



ALPHA1
THE EFFICIENT
CHOICE



ALPHA3
THE INTELLIGENT
CHOICE

Monitoring with GO Remote			<input type="radio"/>
Hydronic balancing with GO Balance		<input type="radio"/>	<input type="radio"/>
Autoadapt		<input type="radio"/>	<input type="radio"/>
Dry-running protection		<input type="radio"/>	<input type="radio"/>
Automatic de-blocking	<input type="radio"/>	<input type="radio"/>	<input type="radio"/>
Low noise level	<input type="radio"/>	<input type="radio"/>	<input type="radio"/>

Source: Sound power values L_{WA} determined according to ISO 20361 ¹⁾, ISO 3745 and ISO 4871.

GRUNDFOS 

Possibility in every drop