

114. Recommended spare parts: SP 17, 30, 46, 60, 77, 95, 125, 160, 215

50/60 Hz, Model B

Recommended spare parts for two to five years' operating time

| Type | Wear parts kit | |
|---------------------|----------------|-----------|
| | Standard | N-version |
| SP 17 1-5 (N) (R) | 96421723 | 96421723 |
| SP 17 6-16 (N) (R) | 96421724 | 96421724 |
| SP 17 17-26 (N) (R) | 96421725 | 96421725 |
| SP 17 27-40 (N) (R) | 96440238 | 96440238 |
| SP 30 1-5 (N) (R) | 96421732 | 96421732 |
| SP 30 6-16 (N) (R) | 96421733 | 96421733 |
| SP 30 17-27 (N) (R) | 96421734 | 96421734 |
| SP 30 28-35 (N) (R) | 96440246 | 96440246 |
| SP 46 2-6 (N) (R) | 96440248 | 96440248 |
| SP 46 7-10 (N) (R) | 96440250 | 96440250 |
| SP 46 11-16 (N) (R) | 96440252 | 96440252 |
| SP 46 17-24 (N) (R) | 96440254 | 96440254 |
| SP 60 2-6 (N) (R) | 96440369 | 96440369 |
| SP 60 7-10 (N) (R) | 96440371 | 96440371 |
| SP 60 11-16 (N) (R) | 96440373 | 96440373 |
| SP 60 17-22 (N) (R) | 96440375 | 96440375 |
| SP 77 1-8 (N) | 96440256 | 96440256 |
| SP 77 9-14 (N) | 96440258 | 96440258 |
| SP 77 15-20 (N) | 96440260 | 96440260 |
| SP 95 1-8 (N) | 96440715 | 96440715 |
| SP 95 9-14 (N) | 96440716 | 96440716 |
| SP 95 15-20 (N) | 96440717 | 96440717 |
| SP 125 1-4 (N) (R) | 96440262 | 96440262 |
| SP 125 5-6 (N) (R) | 96440264 | 96440264 |
| SP 125 7-10 (N) (R) | 96440266 | 96440266 |
| SP 160 1-5 (N) | 205117 | 205117 |
| SP 160 6-9 (N) | 205118 | 205118 |
| SP 215 1-2 (N) | 185033 | 185033 |
| SP 215 3-4 (N) | 185034 | 185034 |
| SP 215 5-7 (N) | 185035 | 185035 |
| SP 215 8-10 (N) | 185036 | 185036 |

Cable termination kit (shrink-flex)

| Kit No | 116251 | 116252 | 116255 | 116253 | 116254 | 116257 | 116258 | 116256 |
|-----------------|------------------------|------------------------|-------------------------|------------------------|------------------------|------------------------|------------------------|------------------------|
| Cable type | Flat cable | | Three single conductors | | Four single conductors | | One single conductor | |
| mm ² | 1.5 - 6 | 6 - 16 | 16 - 25 | 1.5 - 6 | 10 - 25 | 1.5 - 4 | 6 - 16 | 35 - 120 |

| Number of pumps | Number of wear parts kits | Motor complete | Motor cable | Cable termination kit |
|-----------------|---------------------------|----------------|-------------|-----------------------|
| 1-2 | 1 | 1 | 1 | 1 |
| 3-5 | 2 | 1 | 1 | 1 |
| 6-10 | 3 | 1 | 1 | 1 |
| 11-20 | 4 | 2 | 2 | 2 |

Example: Spare parts for four SP 46-10, standard version

2 wear parts kits: [96440250](#)

1 motor complete (see part number in data booklet)

1 motor cable (see part number in data booklet)

1 cable termination kit (see part number in table above)