Correction sheet - DP/EF, SL1/SLV IO, IOS

Addition to Safety Instructions for DP/EF, SL1/SLV, part number 99031641, and correction to Installation and Operating Instructions and Safety Instruction, part number 96526170, 99031641.

Type key SL1.50, SLV.65

Example: SL1.50.65.11.2.1.502

Code	Description	Explanation
SL	Grundfos sewage and wastewater pumps	Pump type
1	Single-channel impeller	Impeller type
V	Free-flow impeller (SuperVortex)	
50	Maximum spherical impeller clearance [mm] Single-channel impeller	Pump passage
65	Maximum solid size [mm] SuperVortex impeller	
65	Nominal diameter of outlet port [mm]	Pump outlet
11	Output power P2 11 = 1.1 kW	Power [kW]
[ ]	Standard	Equipment
[ ]	Standard version	Pump version
Ex	Explosion-proof pump	
2	2-pole	Number of poles
1	Single-phase motor	Number of phases
[ ]	Three-phase motor	
5	50 Hz	Frequency [Hz] [1)]
02	230 V, DOL	Voltage and starting method
0B	400-415 V, DOL	
0C	230-240 V, DOL	
[ ]	1st generation	Generation [2)]
A	2nd generation	
B	3rd generation	
[ ]	Standard	Pump material
Z	Custom-built products	Customisation

[1)] Maximum frequency in case of frequency converter operation.

[2)] The pumps in the individual generations differ in design but are similar in terms of power rating.

中国 RoHS

产品中有害物质的名称及含有信息表

部件名称	有害物质									
	铅 (Pb)	汞 (Hg)	镉 (Cd)	六价铬 (Cr6+)	多溴联苯 (PBBs)	多溴二苯醚 (PBDEs)	邻苯二甲酸二正丁酯（DBP）	邻苯二甲酸二异丁酯 (DIBP)	邻苯二甲酸丁基苄酯（BBP）	邻苯二甲酸二（2-乙基）己酯（DEHP）
泵壳	X	O	O	O	O	O	O	O	O	O
紧固件	X	O	O	O	O	O	O	O	O	O
管件	X	O	O	O	O	O	O	O	O	O
定子	X	O	O	O	O	O	O	O	O	O
转子	X	O	O	O	O	O	O	O	O	O

注 1： O：表示该有害物质在该部件所有均质材料中的含量均不超出电器电子产品有害物质限制使用国家标准要求。
X：表示该有害物质至少在该部件的某一均质材料中含量超出电器电子产品有害物质限制使用国家标准要求。
注 2：以上未列出的部件，表明其有害物质含量均不超出电器电子产品有害物质限制使用国家标准要求。

93456346 06.2025
ECM: 1426459