

ALPHA2

Replacement guide

This list provides you with an easy overview of many of the old circulators that you will meet in your daily work, and with which you can replace with an ALPHA2 from Grundfos. The suggested replacement pumps are ALPHA2 25-40 and 25-60 180mm.



WILO

ALPHA2 25-40	ALPHA2 25-60
Atmos PICO 25/1-4	Atmos PICO 25/1-6
Yonos PICO(plus) 25/1-4	Yonos PICO(plus) 25/1-6
Stratos PICO(plus) 25/1-4	Stratos PICO(plus) 25/1-6
Stratos ECO 25/1-3	Stratos ECO 25/1-5
Smart 25/4	Smart 25/6
Star-EP 25/1-3	Star-EP 25/1-5
Star-E 25/1-3	Star-E 25/1-5
Star-A 25/4	Star-A 25/6
Star-RS 25-4	Star-RS 25-6
RS 25/2 E(n)	RS 25/3 E(n)
RS 25-4	RS 25-6
RS 25/60 r, 25/60 v	5 W - 7 W

And more.

SALMSON

ALPHA2 25-40	ALPHA2 25-60
Priux home 40-25/180	Priux home 60-25/180
SiriuX home 40-25/180	SiriuX home 60-25/180
SiriuX Jr 3m	SiriuX Jr 5m
NXT 33-25 P	NXT 53-25 P (homeson)
NXP 33-25 P	NXP 53-25 P
NXi 33-25 P	NYi 53-25 P (aXess 130mm)
NXL 13-25, 33-25, 43-25 (P)	NXL 53-25, 57-25, 63-25 (P)
MXL 10-25, 12-25, 15-25 (P)	MXL 25-25, 30-25, 50-25 (P)

And more.

Biral

ALPHA2 25-40	ALPHA2 25-60
PrimAX 25-3 180, 25-4 180	PrimAX 25-6 180
AX 10-1, 12-1	AX 13-1
MXE 12-1	MXE 13-1
MX 10-1, 12-1	MX 13-1
ME 12-1	ME 13-1
M 10-1, 12-1	M 13-1
NRB 11-1, 12-1	NRB 13 TE-1
NRB 10 S-1, 11 S-1, 12 S-1	NRB 13 S-1

And more.

DAB

ALPHA2 25-40	ALPHA2 25-60
Evosta3 40/180	Evosta3 60/180
Evosta2 40-70/180 (Speed 1)	Evosta2 40-70/180 (Sp. 2 or 3)
Evotron 40/180	Evotron 60/180
VEA 35/180	VEA 55/180, 65/180
VA 25/180, 35/180	VA 55/180, 65/180
A 35/180	A 55/180, 65/180
RS 25/60 r, 25/60 v	5 W - 7 W

And more.

Grundfos

ALPHA2 25-40	ALPHA2 25-60
ALPHA2 25-40 180	ALPHA2 25-60 180
ALPHA1 25-40 180	ALPHA1 25-60 180
ALPHA2 L 25-40 180	ALPHA2 L 25-60 180
ALPHA Pro 25-40 180	ALPHA Pro 25-60 180
ALPHA+ 25-40 180	ALPHA+ 25-60 180
ALPHA 25-40 180	ALPHA 25-60 180
UPE 25-40 180	UPE 25-60 180
UPE 25-25 180	UPE 25-45 180
UPS 25-40 (-30, -20) 180	UPS 25-60 (25-50) 180
UPS 15-35x20	UPS 15-45x20
UPS 20-35	UPS 20-45, UPS 20-60

And more.

EMB (Switzerland)

ALPHA2 25-40	ALPHA2 25-60
Simplex-Micra 25/1-4	Simplex-Micra 25/1-6
Stratos-Micra 25/1-4	Stratos-Micra 25/1-6
ECO-Star 25/1-3	ECO-Star 25/1-6
Star-E 25/1-3	Star-E 25/1-5
Star-E 25/2	---
RSE 25, 25/4	RSE 25/6
RS 25/2 E(n)	RS 25/3 E(n)
RS 25/2, 25/4	RS 25/6
RP 25/60-2	---
NS 25-25, 25-35	NS 25-55

And more.

KSB

ALPHA2 25-40	ALPHA2 25-60
Calio S 25-40	Calio S 25-60
Riotronic S 25-40	Riotronic S 25-60
Riotronic P 25-40	Riotronic P 25-60
Riotronic ECO 25-40	Riotronic ECO 25-60
Riotronic 25-40	Riotronic 25-60
----	Riotron E 25/1-5
Riomatic C 22/20	Riomatic C 22/35
Rio-Eco N 25-40	Rio-Eco N 25-60
Riovar 22-2 E, 22-3 E	Riovar 22-4 E, 22-5 E, 22-6 E
Rio C 25-15, 25-25, 25-40	Rio C 25-50, 25-60
Rio C 22/25, C 22/40	Rio C 22/50, 22/60
RS 25/60 r, 25/60 v	5 W - 7 W

And more.

LOWARA

ALPHA2 25-40	ALPHA2 25-60
Ecocirc S(+)-25-4/180	Ecocirc M(+)-25-6/180
Ecocirc Premium 25-4/180	Ecocirc Premium 25-6/180
Ecocirc Basic 25-4/180	Ecocirc Basic 25-6/180
Ecocirc 25-4/180	Ecocirc 25-6/180
EV(+)-25-4/180	EV(+)-25-6/180
EA(+)-25-4/180	EA(+)-25-6/180
ETLC 25-4 L	ETLC 25-6 L
ATLC 25-4 L	ETLC 25-6 L
TLC 25-2.5L, 25-4L	TLC 25-5L, 25-6L
ATCR 3	ATCR 5
ETCR 25-3L, ETCR 25-4L	---
TCR 25-4 (L)	TCR 25-5 (L), TCR 25-6
PLM 3 L	TLM 3 L /2
NtLM 3L/2	NtLM 34L/2
RL2S 25-40	RL2S 25-50, 25-60

And more.

For more details

go to www.grundfos.com and type in your pump to be replaced in the replacement tool