

# 85904106 MG160LB 50 Hz

## Sound Measurement Report Sound Power measurement according to DS/ISO-3743

Motor type: MG160LB

Product number: 85904106

Fan diameter: D210 [mm]

P2: 18.5 [kW]

U: 400 [V]

Pole: 2

Frequency: 50 [Hz]


**Remarks:** The declared noise emission value, does not take production variations and measurement uncertainties into account. The declared value may therefore be up-to 3 dB higher, than the value for the average production unit.

Tested at:

### Octave Band Level [db]

| Center Frequency                            | 125  | 250  | 500  | 1000 | 2000 | 4000 | 8000 | dB(A) | dB(lin) |
|---------------------------------------------|------|------|------|------|------|------|------|-------|---------|
| Sound Power<br>Level re: 1 pW               | 63,1 | 65,2 | 68,5 | 69,1 | 66,1 | 63,2 | 60,0 | 73,2  | 74,2    |
| Sound Pressure Average<br>at 1m. re: 20 UPa | 50,6 | 52,7 | 56,0 | 56,6 | 53,6 | 50,7 | 47,5 | 60,7  | 61,8    |

### Sound Pressure calculated according to ISO/DIS 11203 method Q2



Initials: KIR

File no.: LY 27.06.2008