

96571244 MGE90LC 50 Hz

Sound Measurement Report Sound Power measurement according to DS/ISO-3743

Motor type: MGE90LC Product number: 96571244 Fan diameter: D128 [mm]
P2: 2.2 [kW] U: 400 [V] Pole: 2 Frequency: 50 [Hz]


Remarks: The declared noise emission value, does not take production variations and measurement uncertainties into account. The declared value may therefore be up-to 3 dB higher, than the value for the average production unit.

Tested at: 1500 (idle) rpm

Octave Band Level [db]

Center Frequency	125	250	500	1000	2000	4000	8000	dB(A)	dB(lin)
Sound Power Level re: 1 pW	48,6	49,8	52,8	52,9	52,9	45,4	39,8	57,8	59,0
Sound Pressure Average at 1m. re: 20 UPa	36,5	37,8	40,8	40,8	40,9	33,4	27,8	45,8	47,0

Sound Pressure calculated according to ISO/DIS 11203 method Q2



Initials: KIR

File no.: LY05136-02.12.2004