

# 87210321 MG90LC 50 Hz

## Sound Measurement Report Sound Power measurement according to DS/ISO-3743

Motor type: MG90LC Product number: 87210321 Fan diameter: D128 [mm]  
P2: 1.5 [kW] U: 400 [V] Pole: 4 Frequency: 50 [Hz]


**Remarks:** The declared noise emission value, does not take production variations and measurement uncertainties into account. The declared value may therefore be up-to 3 dB higher, than the value for the average production unit.

Tested at:

### Octave Band Level [db]

| Center Frequency                         | 125  | 250  | 500  | 1000 | 2000 | 4000 | 8000 | dB(A) | dB(lin) |
|------------------------------------------|------|------|------|------|------|------|------|-------|---------|
| Sound Power Level re: 1 pW               | 44,1 | 45,8 | 49,6 | 51,5 | 49,4 | 42,6 | 33,9 | 55,2  | 56,1    |
| Sound Pressure Average at 1m. re: 20 UPa | 32,1 | 33,8 | 37,6 | 39,5 | 37,4 | 30,6 | 21,9 | 43,2  | 44,1    |

### Sound Pressure calculated according to ISO/DIS 11203 method Q2



Initials: KIR

File no.: LY19158-13.08.2007