

85901482 MGE180MB 50 Hz

Sound Measurement Report Sound Power measurement according to DS/ISO-3743

Motor type: MGE180MB Product number: 85901482 Fan diameter: D240 [mm]
P2: 22 [kW] U: 400 [V] Pole: 2 Frequency: 50 [Hz]


Remarks: The declared noise emission value, does not take production variations and measurement uncertainties into account. The declared value may therefore be up-to 3 dB higher, than the value for the average production unit.

Tested at: 1500 (idle) rpm

Octave Band Level [db]

Center Frequency	125	250	500	1000	2000	4000	8000	dB(A)	dB(lin)
Sound Power Level re: 1 pW	62,5	61,8	67,6	69,0	68,2	67,2	62,9	74,4	74,9
Sound Pressure Average at 1m. re: 20 UPa	49,8	48,7	54,5	55,9	55,1	54,1	49,8	61,3	61,8

Sound Pressure calculated according to ISO/DIS 11203 method Q2



Initials: KIR

File no.: LY 30.05.2008