

86901883 MG100LB 60 Hz

Sound Measurement Report Sound Power measurement according to DS/ISO-3743

Motor type: MG100LB

Product number: 86901883

Fan diameter: D108 [mm]

P2: 3 [HP]

U: 440 [V]

Pole: 4

Frequency: 60 [Hz]


Remarks: The declared noise emission value, does not take production variations and measurement uncertainties into account. The declared value may therefore be up-to 3 dB higher, than the value for the average production unit.

Tested at:

Octave Band Level [db]

Center Frequency	125	250	500	1000	2000	4000	8000	dB(A)	dB(lin)
Sound Power Level re: 1 pW	45,2	47,3	48,9	52,6	51,0	45,1	37,2	56,4	57,1
Sound Pressure Average at 1m. re: 20 UPa	33,2	35,2	36,9	40,5	38,9	33,0	25,1	44,3	45,0

Sound Pressure calculated according to ISO/DIS 11203 method Q2



Initials: KIR

File no.: LY20075-22.11.2007