

# 87272529 MG100LC 50 Hz

## Sound Measurement Report Sound Power measurement according to DS/ISO-3743

Motor type: MG100LC

Product number: 87272529

Fan diameter: D108 [mm]

P2: 3 [kW]

U: 400 [V]

Pole: 2

Frequency: 50 [Hz]


**Remarks:** The declared noise emission value, does not take production variations and measurement uncertainties into account. The declared value may therefore be up-to 3 dB higher, than the value for the average production unit.

Tested at:

### Octave Band Level [db]

| Center Frequency                            | 125  | 250  | 500  | 1000 | 2000 | 4000 | 8000 | dB(A) | dB(lin) |
|---------------------------------------------|------|------|------|------|------|------|------|-------|---------|
| Sound Power<br>Level re: 1 pW               | 54,3 | 60,4 | 62,2 | 62,4 | 60,7 | 59,1 | 52,5 | 67,3  | 68,4    |
| Sound Pressure Average<br>at 1m. re: 20 UPa | 42,3 | 48,4 | 50,2 | 50,4 | 48,7 | 47,1 | 40,4 | 55,3  | 56,4    |

### Sound Pressure calculated according to ISO/DIS 11203 method Q2



Initials: KIR

File no.: LY15655-29.09.2006