

# 87125208 MG80A 50 Hz

## Sound Measurement Report Sound Power measurement according to DS/ISO-3743

Motor type: MG80A Product number: 87125208 Fan diameter: D89 [mm]  
P2: 0.75 [kW] U: 400 [V] Pole: 2 Frequency: 50 [Hz]


**Remarks:** The declared noise emission value, does not take production variations and measurement uncertainties into account. The declared value may therefore be up-to 3 dB higher, than the value for the average production unit.

Tested at:

### Octave Band Level [db]

| Center Frequency                         | 125  | 250  | 500  | 1000 | 2000 | 4000 | 8000 | dB(A) | dB(lin) |
|------------------------------------------|------|------|------|------|------|------|------|-------|---------|
| Sound Power Level re: 1 pW               | 43,9 | 52,3 | 53,3 | 54,9 | 55,9 | 51,3 | 46,3 | 60,6  | 61,1    |
| Sound Pressure Average at 1m. re: 20 UPa | 32,1 | 40,5 | 41,5 | 43,1 | 44,0 | 39,5 | 34,5 | 48,8  | 49,3    |

### Sound Pressure calculated according to ISO/DIS 11203 method Q2



Initials: KIR

File no.: LY15640-28.09.2006