

85905179 MG80C 60 Hz

| Sound Measurement Report                         |                          |                        |                    |
|--------------------------------------------------|--------------------------|------------------------|--------------------|
| Sound Power measurement according to DS/ISO-3743 |                          |                        |                    |
| Motor type: MG80C                                | Product number: 85905179 | Fan diameter: D89 [mm] |                    |
| P2: 1.1 [kW]                                     | U: 440 [V]               | Pole: 2                | Frequency: 60 [Hz] |


**Remarks:** The declared noise emission value, does not take production variations and measurement uncertainties into account. The declared value may therefore be up-to 3 dB higher, than the value for the average production unit.

**Tested at:**

Octave Band Level [db]

| Center Frequency                         | 125  | 250  | 500  | 1000 | 2000 | 4000 | 8000 | dB(A) | dB(lin) |
|------------------------------------------|------|------|------|------|------|------|------|-------|---------|
| Sound Power Level re: 1 pW               | 48,1 | 56,4 | 59,1 | 58,2 | 60,8 | 56,6 | 52,2 | 65,3  | 65,8    |
| Sound Pressure Average at 1m. re: 20 UPa | 36,3 | 44,6 | 47,3 | 46,4 | 49,0 | 44,8 | 40,4 | 53,5  | 54,0    |

Sound Pressure calculated according to ISO/DIS 11203 method Q2



Initials: KIR

File no.: LY15628-27.09.2006