


ISO 3745

: MGE80B
 U: [V]
 f: [Hz]
 P2: [kW]
 n: [rpm]

: Load: No load / Idle
 f: [Hz]
 P2: [kW]
 n: [rpm]



$L_{pA} : 37.5 \text{ [dB(A)]}$


$L_{WA} : 49.5 \text{ [dB(A)]}$

- L_{WA} IEC 60034-9, ISO 3745, ISO 4871 (IEC 60034-9, ISO 3745 & 4871)
 $K_{WA} = 3 \text{ [dB(A)]}$ (IEC 60064-9; 8)
 (ISO 4871; B2)
- IEC 60034-9 (IEC 60034; 5.2)
 (IEC 60034-9; 6 , Note 2)
- IEC 60034-9 1 가 (IEC 60034-9 1; 7)
- 1m 가 L_{pA} ISO 11203 Q2 (IEC 60034; 5.2)
 S 1 m (ISO 11203; 6.2.3)
 S 가

ISO 3745

: MGE80B
 U: [V]
 f: [Hz]
 P2: [kW]
 n: [rpm]

: Load: No load / Idle
 f: [Hz]
 P2: [kW]
 n: [rpm]



$L_{pA} : 42.5 \text{ [dB(A)]}$


$L_{WA} : 54.5 \text{ [dB(A)]}$

- L_{WA} IEC 60034-9, ISO 3745, ISO 4871 (IEC 60034-9, ISO 3745 & 4871)
 $K_{WA} = 3 \text{ [dB(A)]}$ (IEC 60064-9; 8)
 (ISO 4871; B2)
- IEC 60034-9 (IEC 60034; 5.2)
 (IEC 60034-9; 6 , Note 2)
- IEC 60034-9 1 가 , 가 (IEC 60034-9 1; 7)
- 1m 가 L_{pA} ISO 11203 Q2 (IEC 60034; 5.2)
 S 1 m , (ISO 11203; 6.2.3)
 S 가

ISO 3745

: MGE80B U: [V]
 f: [Hz]
 P2: [kW]
 n: [rpm]

: Load: No load / Idle f: [V]
 f: [Hz]
 P2: [kW]
 n: [rpm]



$L_{pA} : 50.0 \text{ [dB(A)]}$


$L_{WA} : 62.5 \text{ [dB(A)]}$

- L_{WA} IEC 60034-9, ISO 3745, ISO 4871 (IEC 60034-9, ISO 3745 & 4871)
 $K_{WA} = 3 \text{ [dB(A)]}$ (IEC 60064-9; 8)
 (ISO 4871; B2)
- IEC 60034-9 (IEC 60034; 5.2)
 (IEC 60034-9; 6 , Note 2)
- IEC 60034-9 1 가 , 가 (IEC 60034-9 1; 7)
- 1m 가 L_{pA} ISO 11203 Q2 (IEC 60034; 5.2)
 S 1 m ,
 S 가 (ISO 11203; 6.2.3)

ISO 3745

: MGE80B
 U: [V]
 f: [Hz]
 P2: [kW]
 n: [rpm]

: Load: No load / Idle
 f: [Hz]
 P2: [kW]
 n: [rpm]



$L_{pA} : 54.5 \text{ [dB(A)]}$


$L_{WA} : 66.5 \text{ [dB(A)]}$

- L_{WA} IEC 60034-9, ISO 3745, ISO 4871 (IEC 60034-9, ISO 3745 & 4871)
 $K_{WA} = 3 \text{ [dB(A)]}$ (IEC 60064-9; 8)
 (ISO 4871; B2)
- IEC 60034-9 (IEC 60034; 5.2)
 (IEC 60034-9; 6 , Note 2)
- IEC 60034-9 1 가 (IEC 60034-9 1; 7)
- L_{pA} ISO 11203 Q2 (IEC 60034; 5.2)
 S 1 m (ISO 11203; 6.2.3)
 S 가

ISO 3745

: MGE80B U: [V]
 f: [Hz]
 P2: [kW]
 n: [rpm]

: Load: No load / Idle : [V]
 f: [Hz]
 P2: [kW]
 n: [rpm]



$L_{pA} : 59.5 \text{ [dB(A)]}$

$L_{WA} : 71.5 \text{ [dB(A)]}$

- L_{WA} IEC 60034-9, ISO 3745, ISO 4871 (IEC 60034-9, ISO 3745 & 4871)
 $K_{WA} = 3 \text{ [dB(A)]}$ (IEC 60064-9; 8)
 (ISO 4871; B2)
- IEC 60034-9 (IEC 60034; 5.2)
 (IEC 60034-9; 6 , Note 2)
- IEC 60034-9 1 가 (IEC 60034-9 1; 7)
- 1m 가 L_{pA} ISO 11203 Q2 (IEC 60034; 5.2)
 S 1 m (ISO 11203; 6.2.3)
 S 가