

87362278 MG132SB 60 Hz

Sound Measurement Report Sound Power measurement according to DS/ISO-3743

Motor type: MG132SB Product number: 87362278 Fan diameter: D128 [mm]
P2: 10 [HP] U: 440 [V] Pole: 2 Frequency: 60 [Hz]


Remarks: The declared noise emission value, does not take production variations and measurement uncertainties into account. The declared value may therefore be up-to 3 dB higher, than the value for the average production unit.

Tested at:

Octave Band Level [db]

Center Frequency	125	250	500	1000	2000	4000	8000	dB(A)	dB(lin)
Sound Power Level re: 1 pW	63,5	67,5	70,7	71,5	70,9	71,9	63,7	77,6	78,7
Sound Pressure Average at 1m. re: 20 UPa	51,0	55,0	58,2	59,0	58,4	59,4	51,2	65,1	66,2

Sound Pressure calculated according to ISO/DIS 11203 method Q2



Initials: KIR

File no.: LY 02.10.2007