

86D15108 MG100LB 60 Hz

| Sound Measurement Report                         |                          |                         |                    |
|--------------------------------------------------|--------------------------|-------------------------|--------------------|
| Sound Power measurement according to DS/ISO-3743 |                          |                         |                    |
| Motor type: MG100LB                              | Product number: 86D15108 | Fan diameter: D108 [mm] |                    |
| P2: 2.2 [kW]                                     | U: 440 [V]               | Pole: 4                 | Frequency: 60 [Hz] |


**Remarks:** The declared noise emission value, does not take production variations and measurement uncertainties into account. The declared value may therefore be up-to 3 dB higher, than the value for the average production unit.

**Tested at:**

Octave Band Level [db]

| Center Frequency                         | 125  | 250  | 500  | 1000 | 2000 | 4000 | 8000 | dB(A) | dB(lin) |
|------------------------------------------|------|------|------|------|------|------|------|-------|---------|
| Sound Power Level re: 1 pW               | 45,2 | 47,3 | 48,9 | 52,6 | 51,0 | 45,1 | 37,2 | 56,4  | 57,1    |
| Sound Pressure Average at 1m. re: 20 UPa | 33,2 | 35,2 | 36,9 | 40,5 | 38,9 | 33,0 | 25,1 | 44,3  | 45,0    |

Sound Pressure calculated according to ISO/DIS 11203 method Q2



Initials: KIR

File no.: LY20075-22.11.2007