

Integrated Temperature sensor Standard, ITS1

General data




Fig. 1 ITS1 sensor

TM06 1286 2214
TM07 6783 2620

Technical overview

ITS is a temperature sensor from Grundfos Direct Sensors™.

The ITS sensor is fully compatible with wet, aqueous media. The sensor is based on MEMS sensing technology in combination with the corrosion-resistant Silicoat® coating technology on the sensor chip.

Applications

- Pump control
- HVAC systems
- temperature control and chiller systems
- renewable energies such as heat pumps, solar thermals, fresh water and micro-CHP systems
- monitoring and control systems
- water treatment plants
- water utility and distribution systems
- HPC and IT cooling systems.

Features and benefits

- MEMS technology
- direct contact with the aqueous media resulting in a fast response time
- plug and play for quick setup
- smart system solution with Grundfos pump controls
- compact and robust design
- compatible with aqueous media
- suitable for a wide temperature range
- suitable for a wide range of applications.

Temperature range

0-100 °C (32-212 °F)

Certificates



CE



C, CSA, US

Electrical connections




Fig. 2 Electrical connections

TM07 5837 5119

Pin	Description - Analog signal	Colour
1	Do not connect	Yellow
2	Temperature signal 4-20 mA	White
3	GND, 0 V PELV	Green
4	12-30 V supply voltage	Brown

Power supply requirements

- VDC 12-30 V PELV.
- The sensor must be separated from hazardous live circuitry by double or reinforced insulation.
- Grounding of sensor supply is required.

Options



Fig. 3 Different options are available. Cables must be purchased separately.

TM06 6670 2016
TM06 6671 2016

Description	1/2" nipple, stainless steel (316L)
-------------	-------------------------------------

Directives

Grundfos temperature sensors are in conformity with these council directives on the approximation of the laws of the EC member states:

- Low Voltage Directive (2014/35/EU)
 - Standard used: EN 61010-1:2010
- EMC Directive (2014/30/EU)
 - Standards used: EN 61326-1:2013 and EN 61326-2-3:2013

Grundfos Direct Sensors™ are exempted from the Pressure Equipment Directive (PED) according to Article 4, paragraph 3 in the PED 2014/68/EU.

ITS1 0-100



Fig. 4 ITS1 sensor

Dimensions




Fig. 5 Dimensions, RPS

	A	B	C	D	E	F	G
mm	4.5	53.7	27	20	39.9	10.2	14.8
in	3.23	2.11	1.06	0.79	1.57	0.40	0.58

Output signals




Fig. 6 Temperature response

Specifications

Temperature	
Measuring range	0-100 °C (32-212 °F)
Accuracy ($\pm 1 \sigma$), in water, 15-90 °C (59-194 °F), 4 bar	± 0.5 K
Accuracy ($\pm 1 \sigma$), in water, 0-100 °C (32-212 °F), 4 bar	± 1 K
Response time (63.2 %)	< 0.5 s
Resolution	0.3 \pm 0.1 InL K
System conditions and environment	
Liquid types	Aqueous media compatible with wetted materials.
Liquid temperature, operation	0-100 °C (32-212 °F)
Liquid temperature, peak	-10 to +120 °C (14-248 °F), non-freezing
Ambient temperature, operation	-25 to +60 °C (-13 to +140 °F)
Ambient temperature, peak	-55 to +90 °C (-67 to +194 °F)
Humidity, relative	0-95 %, non-condensing
Maximum system pressure	24 bar (348 psi)
Burst pressure	30 bar (435 psi)
Electrical data	
Power supply	12-30 VDC, PELV Grounding of sensor supply required
Analog output signals	4-20 mA
- Temperature	(0 °C at 4 mA and 100 °C at 20 mA)
Power consumption at 0 °C (32 °F), $V_{CC} = 24$ V and $R_L = 147 \Omega$	255 mW
Power consumption at 100 °C (212 °F), $V_{CC} = 24$ V and $R_L = 147 \Omega$	655 mW
Load impedance	See fig. 7
Maximum cable length	3 m (9.1 ft)
Materials	
Sensing element	Silicon-based MEMS
Sealing	EPDM O-rings, FKM O-rings or EPDM sealing cap with FKM O-rings
Housing	Composite, PPS Corrosion-resistant coating, PPS, EPDM or FKM
Wetted materials	Adapter ISO 7/1 - R1/2" and NPT 1/2", EN 1.4408 (AISI 316)
Environmental standards	
Enclosure class	IP44
Temperature cycling	IEC 68-2-14
Vibration, non-destructive	20-2000 Hz, 10 G, 4 h
Electromagnetic compatibility	EN 61326-1




Fig. 7 Minimum supply voltage for a given load resistor

99831435 08.2020

ECM: 1293880