

GRUNDFOS CR 95 - CR 155

# REIMAGINED TO DELIVER MORE

- ✓ More efficiency.
- ✓ More reliability.
- ✓ More performance.

### More cost-efficient

With its optimized hydraulic design — from impeller and guide vanes to inlet, discharge port, sleeve and diffuser — the new generation of Grundfos CR offers world class energy efficiency. Due to its small footprint, it is much easier and less costly to install than other pump designs.


#### More reliable

The new generation of large CR pumps has been made even more robust than its forerunners through use of state-of-the-art technology in simulation-design, materials, testing, and production. Every pump is individually tested before leaving the factory, and reimagined features reduce pump downtime and lower operating costs.

#### **More options**

The new generation adds even more options to what was already the most modular pump program in the world, including higher pressure, lower NPSH and the use of standard motors. And of course, the new CRs are also available as combined systems with dedicated CUE frequency converter and as boosters systems.





#### Material variants PART Impeller/ chamber Pump head Base plate Flanges CR O O O 0 0 CRN O O CRN (H-version\*)

• Stainless steel EN 1.4401 Ouctile cast iron EN-GJS-500-7

O Stainless steel EN 1.4301

\* For corrosive environment



## **Grundfos Express**



# SAVE TIME WITH GRUNDFOS EXPRESS

Grundfos Express lets you find, configure and size pumps online. It is the fastest and easiest way to get exactly what you need.

- Search by application, pump design or pump family
- Configure and select pumps to your exact specification
- Right-size pumps with the intelligent "Quick Size" tool
- Get full documentation including curves, technical specifications, CAD drawings, spare part overview and installation videos

Start at grundfos.portal.intelliquip.com

Visit grundfos.us/pei to learn more about Department of Energy (DOE) pump energy index (PEI) requirements and PEI ratings on specific Grundfos models.

