GRUNDFOS ALPHA2

Circulator pumps 50/60 Hz



1.	General data Circulator pumps Type key Performance range Applications Pumped liquids Control of heating systems Advantages of pump control Automatic Night SetBack Construction Sectional drawing Material specification Motor and control box Pump housing with air separator Installation Electrical data Start-up Liquid temperature System pressure Inlet pressure Setting of pump head Guide to performance curves Curve conditions	3 3 3 4 4 4 5 5 6 6 6 6 6 6 7 7 8 8 8 8 8 8 8 8 10 11 11 11 11 11 11 11 11 11 11 11 11
2.	Technical data ALPHA2 15-50, 15-50 N, 20-50 N (UK) ALPHA2 15-60 (UK)	12 12 13
3.	Accessories Union and valve kits Insulation kits Service kit	14 14 14
4.	Product numbers	15
5.	Further product documentation WebCAPS WinCAPS	16 16 17

1. General data

Circulator pumps

GRUNDFOS ALPHA2 is a complete range of circulator pumps featuring:

- $AUTO_{ADAPT}$ function which suits most installations.
- Integrated differential-pressure control enabling adjustment of pump performance to the actual system requirements.
- · Automatic Night SetBack (selectable).
- Display showing the actual power consumption in Watt
- Motor based on permanent-magnet/compact-rotor technology.

The GRUNDFOS ALPHA2 pump is energy-optimised and complies with the EuP Directive

(EC Commission Regulation No 641/2009) which will be effective as from 1st January 2013.

For GRUNDFOS ALPHA2 pumps, the energy efficiency index (EEI) is \leq 0.23. See page 11.

The installation of a GRUNDFOS ALPHA2 pump will reduce the power consumption considerably, reduce noise from thermostatic valves and similar fittings, and improve the control of the system.

GRUNDFOS ALPHA2 offers a host of advantages:

Energy savings Automatic control of the differential pressure.

Flexibility Suitable for installation in existing systems.

Night setback Automatic Night SetBack(selectable).

Comfort Low-noise operation.

Safety Built-in electrical and thermal protection of the

pump.

Userfriendliness Simple setting and operation.

Type key

Example	ALPHA2	25 - 40	180
Pump range	•		
Nominal diameter (DN) of suction and [mm] (15 = 1"*, 25 = 1 1/2", 32 = 2")	discharge po	rts	
Maximum head [dm]			
: Cast-iron pump housing N: Stainless-steel pump housing A: Pump housing with air separator			
Port-to-port length [mm]			

^{*} Exception: UK version, size 15 = 1 1/2".

Performance range




Fig. 1 Performance range, ALPHA2

TM03 9502 4107

TM03 9890 4507

FM03 9887 4507

Applications

GRUNDFOS ALPHA2 is designed for circulating liquids in heating systems. Pumps with stainless-steel pump housing can also be used in domestic hot-water systems.

GRUNDFOS ALPHA2 is suitable for

- systems with constant or variable flows where it is desirable to optimise the pump duty point.
- · systems with variable flow-pipe temperature.
- · systems where night setback is desired.

GRUNDFOS ALPHA2 is especially suitable for

- installation in existing systems where the differential pressure of the pump is too high during periods of reduced flow demand.
- installation in new systems for fully automatic adjustment of the performance to flow demands without the use of bypass valves or similar expensive components.

Examples of systems




Fig. 2 One-pipe heating system




Fig. 3 Two-pipe heating system




Fig. 4 Underfloor heating system




Fig. 5 Domestic hot-water system

Pumped liquids

TM03 8990 4507

TM03 8989 4507

Clean, thin, non-aggressive and non-explosive liquids, not containing solid particles, fibres or mineral oil.

The pump must not be used for the transfer of flammable liquids such as diesel oil, petrol and similar liquids.

M01 9119 5002

TM01 9120 5002

Control of heating systems

The heating required in a building varies greatly during the day due to changing outdoor temperatures, solar radiation and heat emanating from human beings, electric appliances, etc.

Add to this that the need for heating may vary from one section of the building to another and that the thermostatic valves of some radiators may be turned down by the users.

These circumstances will cause an uncontrolled pump to produce a too high differential pressure when the heating demand is low.

Possible consequences:

- · too high energy consumption
- · irregular control of the system
- · noise in thermostatic valves and similar fittings.

GRUNDFOS ALPHA2 automatically controls the differential pressure by adjusting the pump performance to the actual heating demand, without the use of external components.

AUTO ADAPT

The integrated ${\rm AUTO}_{ADAPT}$ function is especially developed for

- · underfloor heating systems
- two-pipe systems.

The ${\rm AUTO}_{ADAPT}$ function (factory setting) automatically adjusts the pump performance to the demand, i.e. the size of the system and the heating demand. The performance is adjusted gradually over time. An optimum pump setting cannot be expected from day one.

Operation

The $AUTO_{ADAPT}$ function enables the ALPHA2 to control the pump performance automatically:

- Adjustment of the pump performance to the heating demand of the system.
- Adjustment of the pump performance to the variations in load over 24 hours.

In ${\sf AUTO}_{ADAPT}$ mode, the pump is set to proportional-pressure control.




Fig. 6 AUTO_{ADAPT} performance range

The $AUTO_{ADAPT}$ function differs from other control functions as it moves the control curve within a performance range. The shaded area indicates the limits for the movement of the proportional-pressure curve. See fig. 6.

Advantages of pump control

In GRUNDFOS ALPHA2, control is effected by adapting the differential pressure to the flow (proportional- and constant-pressure control). Contrary to an uncontrolled pump, the proportional-pressure-controlled GRUNDFOS ALPHA2 reduces the differential pressure as a result of falling heating demand.

If the heating demand falls - for instance due to solar radiation - the radiator valves will close, and, for the uncontrolled pump, the flow resistance of the system will rise for instance from A_1 to A_2 .

In a heating system with an uncontrolled pump, this situation will cause a pressure rise in the system by ΔH_1 .




Fig. 7 Uncontrolled pump

In a system with a GRUNDFOS ALPHA2 pump, the pressure will be reduced by $\Delta \text{H}_2.$




Fig. 8 Pump in proportional-pressure control mode

In a system with an uncontrolled pump, a pressure rise will often cause flow-generated noise in the thermostatic valves. This noise will be reduced considerably with the GRUNDFOS ALPHA2.

Automatic Night SetBack

GRUNDFOS ALPHA2 features selectable Automatic Night SetBack.

Automatic Night SetBack is activated with the button on the control box.

Factory setting of Automatic Night SetBack: Not active.

Note

If the pump has been set to speed I, II or III, the night setback function is deactivated.

Once Automatic Night SetBack has been activated, the pump automatically changes between normal duty and night setback. Changeover is dependent on the flowpipe temperature measured by the integrated temperature sensor.


Construction

GRUNDFOS ALPHA2 is of the canned-rotor type, i.e. pump and motor form an integral unit without shaft seal and with only two gaskets for sealing. The bearings are lubricated by the pumped liquid.

The pump is characterised by

- integrated AUTO_{ADAPT} control
- integrated proportional-pressure control
- integrated constant-pressure control
- three fixed-speed curves
- frequency converter
- permanent-magnet/compact-stator motor
- display showing the actual pump power consumption in Watt (in whole numbers)
- ceramic shaft and radial bearings
- carbon thrust bearing
- stainless-steel rotor can, bearing plate and rotor cladding
- composite impeller
- cast-iron or stainless-steel pump housing
- compact design featuring pump head with integrated control box and control panel.

Sectional drawing



TM03 9728 4307

Position numbers

Material specification


Pos.	Description	Material	EN/DIN W Nr.	AISI/ ASTM
1	Controller complete	Composite, PC		
9	Rotor can	Stainless steel	1.4301	304
9	Radial bearing	Ceramics		
11	Shaft	Ceramics		
11	Rotor cladding	Stainless steel	1.4301	304
	Thrust bearing	Carbon		
12	Thrust bearing retainer	EPDM rubber		
13	Bearing plate	Stainless steel	1.4301	304
16	Impeller	Composite, PP or PES		
18	Pump housing	Cast iron Stainless steel	EN-JL 1020 EN 1.4308	A48-25 B
	Gaskets	EPDM rubber		

Motor and control box

The motor is a 4-pole synchronous permanent-magnet motor.

The pump controller is incorporated in the control box, which is fitted to the stator housing with two screws and connected to the stator via a terminal plug.

The control box has an integrated control panel with two push-buttons (pos. 1 and 2) and a 2-digit 7segment display.




TM03 8499 4412

Fig. 10 Push-button positions

- Push-button (pos. 1) for selection of control mode.
- Push-button (pos. 2) for activation or deactivation of Automatic Night SetBack.

The light in the display is on when the electricity supply has been switched on. During operation, the display shows the actual pump power consumption in Watt (in whole numbers). Accuracy: ± 5 %.

Faults preventing the pump from operating properly (e.g. blocking) are indicated in the display by "- -". Possible control box positions:



TM03 8497 4412

TM01 9184 1400

Fig. 11 Control box positions

The cable entry incorporates cable relief.




Fig. 12 Cable entry with cable relief

Pump housing with air separator

The pump housing with air separator is installed in systems where the liquid contains so much air that a circulator pump without air separator cannot start or keep up a continuous circulation. The pump housing is available only for upward water flows.

The air-containing liquid is guided from the suction port to the nozzle of the air-separating chamber and caused to circulate considerably in the relatively large chamber, thus creating a relatively lower pressure at the back (top) of the chamber. This lower pressure combined with the reduced velocity of the liquid in the air-separating chamber will cause a separation of air from the liquid. Due to its lower density, the air will escape through an automatic air vent fitted to the air-separating chamber.

The pump housing has an Rp 3/8 tapping for fitting of an air vent. The air vent is not supplied with the pump.




Fig. 13 Pump housing with air-separating chamber




Fig. 14 Air separation

TM00 9101 1097

TM03 8498 1707

Installation

In most cases, the installation of the ALPHA2 is reduced to the mechanical installation and the connection to the electricity supply.

The pump must always be installed with horizontal motor shaft.




Fig. 15 Horizontal motor shaft

Electrical data

Supply voltage	1 x 230 V - 10 %/+ 6 %, 50 Hz, PE
Motor protection	The pump requires no external motor protection.
Enclosure class	IP 42
Insulation class	F
Relative air humidity	Maximum 95 %
Ambient temperature	0 °C to +40 °C
Temperature class	TF110 to CEN 335-2-51
EMC (electromagnetic compatibility)	EN 61000-6-2 and EN 61000-6-3
Sound pressure level	≤ 43 dB(A)

Start-up

The pump must not be started until the system has been filled with liquid and vented. Furthermore, the required minimum inlet pressure must be available at the pump inlet. The system cannot be vented through the pump.

The pump is self-venting. It need not be vented before start-up.

Liquid temperature

Cast-iron pumps: +2 °C to +110 °C.

Stainless-steel pumps in domestic hot-water systems: $+15~^{\circ}\text{C}$ to $+65~^{\circ}\text{C}$.

In domestic hot-water systems, it is recommended to keep the liquid temperature below 65 °C to eliminate the risk of lime precipitation.

To avoid condensation in the control box and stator, the liquid temperature must always be higher than the ambient temperature. See table.

Ambient temperature	Liquid temperature					
[,c]	Min. [°C]	Max. [°C]				
0	2	110				
10	10	110				
20	20	110				
30	30	110				
35	35	90				
40	40	70				

System pressure

PN 10: Maximum 1.0 MPa (10 bar).

Inlet pressure

TM03 8501 1707

To avoid cavitation noise and damage to the pump bearings, the following minimum pressures are required at the pump suction port.

	Liquid temperature	•
75 °C	90 °C	110 °C
0.5 m head	2.8 m head	10.8 m head

Setting of pump head

With the push-button on the control box, the electronically controlled pump can be set to the following:

- AUTO_{ADAPT} operating area
- two constant-pressure curves
- two proportional-pressure curves
- three fixed-speed curves.

Factory setting

The push-button on the pump control box is factory-set as shown in the table below.

This setting is suitable for a large majority of all single-family houses.

Pump type	Setting	Automatic Night Setback
ALPHA2 xx-40		
ALPHA2 xx-50	AUTO _{ADAPT}	Deactivated
ALPHA2 xx-60	,,,,,,,	

Change of performance

The pump performance (flow and head) can be changed by pressing the control box push-button as indicated in the table below and fig. 16.




Fig. 16 Pump setting in relation to performance

Setting	Pump curve	Function
AUTO _{ADAPT} (factory setting)	Highest to lowest proportional-pressure curve	The AUTO _{ADAPT} function enables ALPHA2 to control the pump performance automatically within a defined performance range, see fig. 16: • Adjusting the pump performance to the size of the system. • Adjusting the pump performance to the variations in load over time. In AUTO _{ADAPT} , the pump is set to proportional-pressure control.
PP1	Lowest proportional- pressure curve	The duty point of the pump will move up or down on the lowest proportional-pressure curve, see fig. 16, depending on the heat demand. The head (pressure) is reduced at falling heat demand and increased at rising heat demand.
PP2	Highest proportional- pressure curve	The duty point of the pump will move up or down on the highest proportional-pressure curve, see fig. 16, depending on the heat demand. The head (pressure) is reduced at falling heat demand and increased at rising heat demand.
CP1	Lowest constant- pressure curve	The duty point of the pump will move out or in on the lowest constant-pressure curve, see fig. 16, depending on the heat demand in the system. The head (pressure) is kept constant, irrespective of the heat demand.
CP2	Highest constant- pressure curve	The duty point of the pump will move out or in on the highest constant-pressure curve, see fig. 16, depending on the heat demand in the system. The head (pressure) is kept constant, irrespective of the heat demand.
III	Speed III	ALPHA2 runs at a constant speed and consequently on a constant curve. In speed III, the pump is set to run on the max. curve under all operating conditions. See fig. 16. Quick venting of the pump can be obtained by setting the pump to speed III for a short period.
II	Speed II	ALPHA2 runs at a constant speed and consequently on a constant curve. In speed II, the pump is set to run on the medium curve under all operating conditions. See fig. 16.
1	Speed I	ALPHA2 runs at a constant speed and consequently on a constant curve. In speed I, the pump is set to run on the min. curve under all operating conditions. See fig. 16.
*)	*)	ALPHA2 changes to the curve for Automatic Night SetBack, i.e. absolute minimum performance and power consumption, provided certain conditions are met. See <i>Automatic Night SetBack</i> .

TM03 9208 3607

Guide to performance curves

Each pump setting has its own performance curve (Q/H curve). However, AUTO_{ADAPT} covers a performance range.

A power curve (P1 curve) belongs to each Q/H curve. The power curve shows the pump power consumption (P1) in Watt at a given Q/H curve.

The P1 value corresponds to the value that can be read from the pump display. See fig. 17.




Fig. 17 Performance curves in relation to pump setting

Setting	Pump curve
AUTO _{ADAPT} (factory setting)	Setpoint within the shaded area
PP1	Lowest proportional-pressure curve
PP2	Highest proportional-pressure curve
CP1	Lowest constant-pressure curve
CP2	Highest constant-pressure curve
III	Constant speed, speed III
II	Constant speed, speed II
1	Constant speed, speed I
*)	Curve for Automatic Night SetBack

Curve conditions

The guidelines below apply to the performance curves on the next pages:

- · Test liquid: airless water.
- The curves apply to a density of ρ = 983.2 kg/m³ and a liquid temperature of +60 °C.
- All curves show average values and should not be used as guarantee curves. If a specific minimum performance is required, individual measurements must be made.
- The curves for the speeds I, II and III are marked.
- The curves apply to a kinematic viscosity of υ = 0.474 mm²/s (0.474 cSt).
- The conversion between head H [m] and pressure p [kPa] has been made for water with a density of ρ = 1000 kg/m³. For liquids with other densities, e.g. hot water, the discharge pressure is proportional to the density.

Symbols used on the following pages




TM05 6076 4412

Fig. 18 Energy efficiency index (EEI)

The GRUNDFOS ALPHA2 pump is energy-optimised and complies with the EuP Directive (EC Commission Regulation No 641/2009) which will be effective as from 1st January 2013.

For GRUNDFOS ALPHA2 pumps, the energy efficiency index (EEI) is \leq 0.23.



TM05 3936 1712

Fig. 19 Old energy label


On 1st January 2013, the old A to G energy label will be replaced by the new energy efficiency index (EEI). Only the best of today's A-labelled circulator pumps will meet the new requirements.

The ALPHA2 with its ${\rm AUTO}_{ADAPT}$ function is the preferred choice for domestic installations and a true efficiency frontrunner.

The energy efficiency index (EEI) is the difference between the annual energy consumption of the ALPHA2 and the standard consumption of a typical similar model.

The ${\rm AUTO}_{ADAPT}$ function ensures an energy consumption that is even lower than the indicated EEI, but due to the calculation method, this is not reflected in the EEI

The ALPHA2 EEI is lower than the EuP 2013 and 2015 requirements.



TM05 6095 4512

Fig. 20 EEI limits

For more information about the new energy directive, please visit:




energy.grundfos.com

2. Technical data

ALPHA2 15-50, 15-50 N, 20-50 N (UK)

1 x 230 V, 50/60 Hz






 Speed
 P1 [W]
 I_{1/1} [A]


 Min.
 5
 0.05

 Max.
 32
 0.27

Connections: System pressure: Liquid temperature: See "Union and valve kits" on page 14. Max. 1.0 MPa (10 bar). +2 °C to +110 °C (TF 110).

The pump incorporates overload protection.






TM03 9215 3607

Pump type					Dim	ensions	mm]				Weigl	nts [kg]	Ship. vol.
rump type	EEI≤	L1	B1	B2	В3	B4	H1	H2	Н3	G	Net	Gross	[m ³]
ALPHA2 15-50	0.20	130	78	78	46	49	27	127	58	1 1/2	1.9	2.1	0.00383
ALPHA2 15-50 N	0.20	130	-	-	47	48	26	127	-	1 1/2	2.8	3.0	0.00383
ALPHA2 20-50 N	0.20	150	-	-	49	49	28	127	-	1 1/4	2.9	3.1	0.00383

ALPHA2 15-60 (UK)

1 x 230 V, 50/60 Hz





TM03 9085 3307 - TM05 2085 4411

Speed	P1 [W]	I _{1/1} [A]
Min.	5	0.05
Max.	45	0.38

Connections: System pressure: Liquid temperature:


Also available with:


See "Union and valve kits" on page 14. Max. 10 bar.

+2 °C to +110 °C (TF 110).

Stainless-steel pump housing, type N (only ALPHA2 25-60 N 180).

The pump incorporates overload protection.





TM03 9215 3607

Pump type					Dim	ensions	mm]				Weigl	nts [kg]	Ship. vol.
i unip type	EEI≤	L1	B1	B2	В3	В4	H1	H2	Н3	G	Net	Gross	[m ³]
ALPHA2 15-60	0.23	130	77	78	46	49	27	129	58	1 1/2	1.9	2.1	0.00383

3. Accessories

Union and valve kits

Pump type	Description	Material	Product number
	3/4" unions	Cast iron	529921
ALPHA2 25-40, 25-40 A, 25-50,	1" unions	Cast iron	529922
25-60, 25-60 A	3/4" valves	Brass	519805
	1" valves	Brass	519806
	3/4" unions	Brass	529971
ALPHA2 25-40 N,	1" unions	Brass	529972
25-60 N	3/4" valves	Brass	519805
	1" valves	Brass	519806
ALPHA2 32-40,	1" unions	Cast iron	509921
32-60	1 1/4" unions	Cast iron	509922

Insulation kits

GRUNDFOS ALPHA2 can be fitted with two insulating shells.

The insulation thickness of the insulating shells corresponds to the nominal diameter of the pump.

The insulation kit, which is tailored to the individual pump type, encloses the entire pump housing. The two shells are easily fitted around the pump.





Fig. 21 Insulating shells

Pump type	Product number		
ALPHA2 15-40, 15-60, 25-40, 32-40, 25-50, 25-60, 32-60	505821		
ALPHA2 25-40 A, 25-60 A	505822		

Service kit



Description	Product number		
Plug	595562		

4. Product numbers

ALPHA2 (for the UK market)

Pump type	Port-to-port length [mm]	Connection	Voltage [V] 50 Hz	Product number	Insulating kit	Data sheet
ALPHA2 15-50				95047509	E0E004	page 12
ALPHA2 15-60	130	G 1 1/2	230	95047510	505821	page 13
ALPHA2 15-50 N			230	95047511		222 10
ALPHA2 20-50 N	150	G 1 1/4		95047534	-	page 12

5. Further product documentation

WebCAPS




WebCAPS is a Web-based Computer Aided Product Selection program available on www.grundfos.com.

WebCAPS contains detailed information on more than 220,000 Grundfos products in more than 30 languages.

Information in WebCAPS is divided into six sections:

- Catalogue
- Literature
- Service
- Sizing
- Replacement
- CAD drawings.



Catalogue (



Based on fields of application and pump types, this section contains the following:

- technical data
- curves (QH, Eta, P1, P2, etc.) which can be adapted to the density and viscosity of the pumped liquid and show the number of pumps in operation
- product photos
- dimensional drawings
- wiring diagrams
- quotation texts, etc.




Literature (



This section contains all the latest documents of a given pump, such as

- data booklets
- installation and operating instructions
- service documentation, such as Service kit catalogue and Service kit instructions
- quick guides
- product brochures.



Service (3)

This section contains an easy-to-use interactive service catalogue. Here you can find and identify service parts of both existing and discontinued Grundfos pumps.

Furthermore, the section contains service videos showing you how to replace service parts.




Sizing (

This section is based on different fields of application and installation examples and gives easy step-by-step instructions in how to size a product:

- Select the most suitable and efficient pump for your installation.
- Carry out advanced calculations based on energy, consumption, payback periods, load profiles, life cycle costs,
- Analyse your selected pump via the built-in life cycle cost tool. Determine the flow velocity in wastewater applications, etc.



Replacement (



The section contains replacement data of a wide range of pumps produced by other manufacturers than Grundfos.

Based on an easy step-by-step guide, you can compare Grundfos pumps with the one you have installed on your site. When you have specified the installed pump, the guide will suggest a number of Grundfos pumps which can improve both comfort and efficiency.



CAD drawings (ff)

In this section, it is possible to download 2-dimensional (2D) and 3-dimensional (3D) CAD drawings of most Grundfos pumps.

These formats are available in WebCAPS:

- 2-dimensional drawings:
- .dxf, wireframe drawings
- .dwg, wireframe drawings.
- 3-dimensional drawings:.dwg, wireframe drawings (without surfaces)
- .stp, solid drawings (with surfaces)
- .eprt, E-drawings.

WinCAPS



Fig. 23 WinCAPS DVD

WinCAPS is a Windows-based Computer Aided Product Selection program containing detailed information on more than 220,000 Grundfos products in more than 30 languages.

The program contains the same features and functions as WebCAPS, but is an ideal solution if no internet connection is available.

WinCAPS is available on DVD and updated once a year.

Subject to alterations.

BE > THINK > INNOVATE >

96769610 1112

ECM: 1103184

The name Grundfos, the Grundfos logo, and the payoff **be think innovate** are registered trademarks owned by Grundfos Holding A/S or Grundfos A/S, Denmark. All rights reserved worldwide.

